## HITPOINT TEL:8862-26013311 FAX:8862-26013898

NO.4 Lane 505, Zhongzheng Rd,. Linkou Shiang, Taipei, Taiwan 24445 . R.O.C

## Piezo Siren

### **PS-520Q**

(ROHS)


DATE:2009.06.05

**1** . Electrical Characteristics

VER .:3

Resonant Frequency (KHz)	3.0 ±0.5	
Operating Voltage (Vdc)	5 ~ 15	
Rated Voltage (Vdc)	12	
Current Consumption (mA/max.)	200 at Rated Voltage	
Sound Pressure Level (dB/min.)	105 at 100cm at Rated Voltage	
Tone/Pulse Rate (Hz)	Constant	
Operating Temperature (°C)	-20 ~ +70	
Storage Temperature (°C)	-30 ~ +80	

#### 2 . Dimensions and Material 2-1 Shape



Unit : mm

# HITPOINT

NO.4 Lane 505, Zhongzheng Rd, Linkou Shiang, Taipei, Taiwan 24445 . R.O.C

#### 2-2 Material

Housing	ABS 757 UL94HB plastic resin (Color : Black)
Leading Wire	20 AWG
Weight (Gram)	52.2


#### **3. TESTING METHOD**

#### · Standard Measurement conditions

Temperature:25±2 °C Humidity:45-60%

#### · Acoustic Characteristics

The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below.





#### 4. RELIABILITY

ITEMS	METHOD OF TEST AND MEASUREMENTS	PERFORMANCE
Coldness	After 98 hours of being exposed to -30 $^{\circ}\!C$	No abnormality
withstanding	environment, should be returned to normal	shall exist
	environment for 2 hours, then re-proceed to test.	
Hotness	After 98 hours of being exposed to +80 ${}^\circ\!{}^\circ\!{}^\circ$	No abnormality
withstanding	environment, should be returned to normal	shall exist
	environment for 2 hours, then re-proceed to test.	
Humidity	After 98 hours of being exposed to 40 $^{\circ}\!\!\!\!\!\!C$ 95%RH	No abnormality
withstanding	environment in actual operation, should be	shall exist
	returned to normal environment for 2 hours, then	
	re-proceed to test.	
Durability	10sec on/10sec off ; 1000hours(180000 cycles)	No abnormality
		shall exist
Vibration	Linear vibrate frequency rate: 5~55Hz	No abnormality
withstanding	Time:180sec , applied in X, Y and Z directions for	shall exist
	3 times each.	

#### 5. PACKAGE METHOD

- <1> One inner box consists of 1pcs.
- <2> 250pcs of PS-520 Qare packed in a carton box. (L\*W\*H=520\*335\*290mm)
- <3> N . W . : ; 13.1KGS ; G . W . : 17.5KGS ;
- <4> RoHS Mark: